Contact our sales office for delivery dates and prices as this is a special model.

Specialized Product **P.G.** Point to Group information

5-Port Solenoid Valve

with Single/Double Switch Function

SY3$^{S}_{D}$00/SY5$^{S}_{D}$00



Features

Choose between single and double solenoids by using the switch!



Applicable cylinder speed	Main valve seal type	Series	Applicable cylinder											
			ø6	ø10	ø16	ø20	ø25	ø32	ø40	ø50	ø63	ø80	ø100	ø125
100 mm/s or less	Rubber seal	SY3$^{S}_{D}$00										●		
300 mm/s or less										●				
100 mm/s or less		SY5$^{S}_{D}$00												●
300 mm/s or less											●			

[Common conditions]

● Pressure: 0.5 MPa ● Piping length: 1 m ● Load ratio: 50% ● Stroke: 200 mm

Connector-type manifold (for side and bottom-ported types)

∗ Use as a guide for selection. Please check the actual conditions with SMC's Model Selection Software.

⚠ Caution To ensure the safest possible operation of this product, please be sure to thoroughly read the **"Safety Instructions"** in our "Best Pneumatics" catalog before use.

SMC Corporation 4-14-1, SOTO-KANDA, CHIYODA-KU, TOKYO 101-0021, JAPAN **URL: http://www.smcworld.com**

©2017 SMC Corporation All Rights Reserved

SP161X-007E
P: VQ