

! Contact our sales office for delivery dates and prices as this is a special model.

Specialized Product

Point to Group
P.G. information

Electric Actuator with Protective Cover: Slider Type, Ball Screw Drive

LEFS32-X1033

Step Motor (Servo/24 VDC) Type


Features

A protective cover has been added to the upper surface of the body.

Protects the actuator by preventing water droplets and dust from entering from the upper surface

Now with a seal connector

Prevents the intrusion of water droplets and dust from between the cable and the motor cover



Now with an added seal

A seal has been added to the joining portion of the components. Prevents the intrusion of water droplets and dust into the product

Step Motor (Servo/24 VDC) Controller/Driver

▶ Step Data Input Type LECP6 Series

- 64 positioning points
- Input using teaching box or controller setting kit



▶ CC-Link Direct Input Type LECPMJ Series



▶ Programless Type LECP1 Series

- 14 positioning points
- Control panel setting



▶ Pulse Input Type LECPA Series



⚠ Caution

To ensure the safest possible operation of this product, please be sure to thoroughly read the "Safety Instructions" in our "Best Pneumatics" catalog before use.